

**Membrane Element ESPA3-4040** 3000 gpd (11.4 m<sup>3</sup>/d) **Performance:** Permeate Flow: Salt Rejection: 98.5 % Configuration: Spiral Wound Membrane Polymer: Composite Polyamide 85 ft<sup>2</sup> (7.9m<sup>2</sup>) Membrane Active Area: **Application Data\*** 600 psig (4.16 MPa) Maximum Applied Pressure: < 0.1 PPM Maximum Chlorine Concentration: 113 °F (45 °C) Maximum Operating Temperature:

pH Range, Continuous (Cleaning): 3.0-10.0 Maximum Feedwater Turbidity: 1.0 NTU Maximum Feedwater SDI (15 mins): 5.0 Maximum Feed Flow: 16 GPM (3.6 m<sup>3</sup>/h)

Minimum Ratio of Concentrate to Permeate Flow for any Element: 5:1 Maximum Pressure Drop for Each Element: 10 psi


The limitations shown here are for general use. The values may be more conservative for specific projects to ensure the best performance and longest life of the membrane.

## **Test Conditions**

**Type** 

The stated performance is initial (data taken after 30 minutes of operation), based on the following conditions:

1500 PPM NaCl solution 150 psi (1.05 MPa) Applied Pressure 77 °F (25 °C) Operating Temperature 15% Permeate Recovery 6.5 - 7.0 pH Range (Data taken after 30 minutes of operation)



Weight, lbs. (kg) A, inches (mm) B, inches (mm) C, inches (mm) 0.75 (19.1) 40.0 (1016) 3.95 (100.3) 8 (2.3)

Core tube extension = 1.05" (26.7 mm)

Permeate flow for individual elements may vary +25 or - 15 percent. All membrane elements are supplied with a brine seal, interconnector, and o-rings. Elements are enclosed in a sealed polyethylene bag containing less than 1.0% sodium meta-bisulfite solution, and then packaged in a cardboard box. All elements are guaranteed 99.4% minimum rejection.

Hydranautics believes the information and data contained herein to be accurate and useful. The information and data are offered in good faith, but without guarantee, as conditions and methods of use of our products are beyond our control. Hydranautics assumes no liability for results obtained or damages incurred through the application of the presented information and data. It is the user's responsibility to determine the appropriateness of Hydranautics' products for the user's specific end

For information contact: Tel. +31-15-26.10.900 info@lenntech.com www.lenntech.com Fax. +31-15-26.16.289