




	Membrane Element	CPA2-4040
Performance:	Permeate Flow: Salt Rejection :	2,250 gpd (8.5 m ³ /d) 99.5% (99.2% minimum)
Туре	Configuration: Membrane Polymer: Membrane Active Area:	Spiral Wound Composite Polyamide 85 ft ² (7.9 m ²)
Application Data*	Maximum Applied Pressure: Maximum Chlorine Concentration: Maximum Operating Temperature: pH Range, Continuous (Cleaning): Maximum Feedwater Turbidity: Maximum Feedwater SDI (15 mins): Maximum Feed Flow: Minimum Ratio of Concentrate to Permeate Flow for any Element: Maximum Pressure Drop for Each Element:	600 psig (4.14 MPa) < 0.1 PPM 113 °F (45 °C) 2-10 (1-12)* 1.0 NTU 5.0 16 GPM (3.6 m ³ /h) 5:1 15 psi

* The limitations shown here are for general use. For specific projects, operating at more conservative values may ensure the best performance and longest life of the membrane. See Hydranautics Technical Bulletins for more detail on operation limits, cleaning pH, and cleaning temperatures.

Test Conditions

The stated performance is initial (data taken after 30 minutes of operation), based on the following conditions:

1500 PPM NaCl solution 225 psi (1.55 MPa) Applied Pressure 77 °F (25 °C) Operating Temperature 15% Permeate Recovery 6.5 - 7.0 pH Range



Nonce: Permeate now for individual elements may vary + 35 or - 15 percent. All memorane elements are supplied with a bine seal, interconnector, and o-imgs. Elements are enclosed in a sealed polyethylene bag containing less than 1.0% sodium meta-bisulfite solution and 10% propylene glycol, and then packaged in a cardboard box.

Hydranautics believes the information and data contained herein to be accurate and useful. The information and data are offered in good faith, but without guarantee, as conditions and methods of use of our products are beyond our control. Hydranautics assumes no liability for results obtained or damages incurred through the application of the presented information and data. It is the user's responsibility to determine the appropriateness of Hydranautics' products for the user's specific end uses. 3/06/2015

LENNTECH info@lenntech.com Tel. +31-152-610-900 www.lenntech.com Fax. +31-152-616-289