



PRODUCT SPECIFICATION


RO TurboClean® Element For Dialysis and High-Purity Applications

Model	Permeate Flow*	Average Salt Rejection	Minimum Salt Rejection
TurboClean® HP 4040-RO-F	2,400 GPD (9.1 m ³ /d)	99.5%	98.5%

* Performance is based on the following test conditions: 2,000 ppm NaCl, 225 psi, 77°F (25°C), 15% recovery, pH 8.0, 30 minutes operation. Individual element permeate flow may vary +/- 15%.

OPERATIONAL AND DESIGN DATA

Membrane Type	ACM Fully Aromatic Polyamide Advanced Composite Membrane
Configuration	Spiral Wound, Sanitary Style Element
Active Membrane Area	80 ft ² (7.4 m ²)
Typical Applied Pressure.....	150 - 300 psi (10 - 21 bar)
Maximum Applied Pressure	600 psi (41 bar)
Maximum Operating Temperature.....	113°F (45°C)
Feed pH Range.....	2 - 11 continuous
Chlorine Tolerance	<0.1 ppm
Maximum Feed Flow	20 GPM (4.5 m ³ /hr)
Maximum Pressure Drop.....	15 psi (1 bar) per element; 60 psi (4 bar) across housing
Maximum Feed SDI (15 minutes).....	5.0
Maximum Feed Turbidity	1 NTU
Application	High Purity Water
Part Number.....	164050442
Replaces Model(s).....	4040-M2P3U5, 4040-ACM2-TSS



Element Weight: 15 lbs. (7 kg)

Length (A): 40.0" (1,016 mm) Diameter (B): 4.0" (101 mm)

Permeate Tube (C): 0.62" (15.9 mm)

Permeate Tube: Desal Style tube; "Flush-ended" design

Feed Spacer: 0.031" thick diamond spacer



**Engineered Membrane
SOLUTIONS**

LENNTech

info@lenntech.com Tel. +31-152-610-900

www.lenntech.com Fax. +31-152-616-289