

Item	Part number	Q-ty	Title	Material	
1	16-4-1200	1	Body of PV	GFRP	
2	044-405-1201	2	Side port 4"	Super duplex stainless steel	
3	285772409	4	Retaining ring	Stainless steel	
4	006-406-1205	2	Disk for port	Stainless steel	
5	014-400-0709	2	Seal for port	EPDM	
6	005-661-1200	2	Support ring	Aluminum	
7	003-165-1200	2	Base plate	Aluminum	
8	007-402-0084	2	Seal for S.plate	EPDM	
9	013-165-1200	2	Sealing plate	Engineering plastic	
10	011-420-1202	2	Retaining ring	Stainless steel	
11	007-112-0053	2	Seal for P.port	EPDM	
12	008-160-1204	2	Permeate port	Engineering plastic	
13	004-165-1041	1	Thrust ring	Engineering plastic	
14	007-085-0053	2	Seal for adapter	EPDM	
15	As required	2	Adapter	Engineering plastic	
16	As required	2	Membrane seal	EPDM	
17	010-160-9001	3	Spacer 1mm.	Engineering plastic	
18	010-160-9005	2-8	Spacer 5mm.	Engineering plastic	
19	016-002-0845	8	Socket screw	Stainless steel	
20	015-160-0000	2	Strap assy.	Stainless steel	
21	012-160-0000	2-3	Saddle	Engineering plastic	
22					
23					
24					

of the general statement of use and technical manual

Shell	L (l.o.a.),	P, port to port mm.	M, length for	S#	w
length	mm.		membrane	(span)	weight
code	inch		elements,	mm.	_
code	IIICII	IIICII	mm. / inch	inch	kg. lb.
1	2303	1407	1107	700	401
	90.67	55.39	43.6	27.6	884
2	3335	2439	2139	1700	465
2	131.30	96.02	84.2	66.9	1025
3	4367	3471	3171	2700	529
3	171.93	136.65	124.8	106.3	1166
4	5399	4503	4203	3420	593
7	212.56	177.28	165.5	134.6	1307
5	6431	5535	5235	4450	656
3	253.19	217.91	206.1	175.2	1448
6	7463	6567	6267	5470	720
0	293.82	258.54	246.7	215.4	1588
7	8495	7599	7299	6500	784
1	334.45	299.17	287.4	255.9	1729
8	9527	8631	8331	7530	848
0	375.08	339.80	328	296.5	1870

info@lenntech.com Tel. +31-152-610-900 www.lenntech.com Fax. +31-152-616-289

Notes:

- 1. All dimensions are for reference only, not for construction unless certified. Dimensions L, P, M can be varied according to exact membrane type.
- 2. Item 17 & 18 should be located on feed side for membranes shimming.
- 3. Item 13 downstream only.
- 4. Item 19 closing torque not to exceed 2 Nm.
- 5. Drawing unit: mm. (inches).
- 6. Saddles can be shimmed if required.
- 7. The vessel is supplied with two straps for external saddles.
- 8. Do not scale drawing, may be reprinted on any paper size or copied.

Warning.

- 1. Never pressurize a pressure vessel that was not loaded with membrane elements.
- 2. Wrong manifolding may cause an excessive pressure on port what can lead to leaks.
- 3. Max. allowable working pressure not to exceed 1200 psi. (82.7 bar).
- 4. Permeate internal pressure not to exceed 125 psi. (8.6 bar).
- 5. Operating temperature not to exceed 49°C (120°F).

BE		BEL 16-s(2x4)-1200 psi.		Daria P.	15/08/2014
	BEL	RO PRESSURE VESSEL	CHECK	Yuri V.	15/08/2014
	DRAWING Nº.	16s4-1200	APPR.	Ari A.	15/08/2014
		NG IS PROPERTY OF BEL GROUPLIMITED IT IS STRICTLY FORBIDDEN OR DISCLOSE ANY PART OF IT TO THIRD PARTY WITHOUT WRITTEN		Sheet 1 Of 1	REV.: 0