

RE 16040-BLF

Low pressure grade RO element for brackish water

CSM[®]

LENNTECH

info@lennotech.com Tel. +31-152-610-900

www.lennotech.com Fax. +31-152-616-289

SPECIFICATIONS :

General Features	Permeate flow rate:	46,000 GPD (174.1 m ³ /day)
	Nominal salt rejection:	99.2%
	Effective membrane area:	1,600 ft ² (148.6 m ²)

- The stated product performance is based on data taken after 30 minutes of operation at the following test conditions:
 - 500 mg/L NaCl solution at 100 psig (0.7 MPa) applied pressure
 - 15% recovery
 - 77 °F (25 °C)
 - pH 6.5 –7.0
- Minimum salt rejection is 99.0%.
- Permeate flow rate for each element may vary but will be no more than 15%.
- All elements are vacuum sealed in a polyethylene bag containing 1.0% SBS (sodium bisulfite) solution and individually packaged in a cardboard box.

Membrane type:	Thin-Film Composite
Membrane material:	Polyamide(PA)
Element configuration:	Spiral-Wound, FRP Wrapping

Dimensions and Weight

Model Name	A	B	C	Weight	Part Number	
					Inter - connector	O-ring
RE16 040-BLF	40.0 inch (1,016 mm)	16.0 inch (402 mm)	3.0 inch (77 mm)	60 kg	40000219	40000220



- Each membrane element supplied with one interconnector (coupler) and five o-rings.
- All RE 16040 elements fit nominal 16.0 inch (402 mm) I.D. pressure vessels.

The information provided in this document is solely for informative purposes. It is the user's responsibility to ensure the appropriate usage of this product. Woongjin Chemical assumes no obligation, liability or damages incurred for the misuse of the product or for the information provided in this document. This document does not express or imply any warranty as to the merchantability or fitness of the product.

RE16 040-BLF

Low pressure grade RO element for brackish water



APPLICATION DATA :

Operating Limits	· Max. Pressure Drop / Element	15 psi (0.1 MPa)
	· Max. Pressure Drop / 240" Vessel	60 psi (0.41 MPa)
	· Max. Operating Pressure	600 psi (4.14 MPa)
	· Max. Feed Flow Rate	252 gpm (97.2 m ³ /hr)
	· Min. Concentrate Flow Rate	64 gpm (24.5 m ³ /hr)
	· Max. Operating Temperature	113 °F (45 °C)
	· Operating pH Range	2.0–11.0
	· CIP pH Range	1.0–13.0
	· Max. Turbidity	1.0 NTU
	· Max. SDI (15 min)	5.0
· Max. Chlorine Concentration	< 0.1 mg/L	

Saturation Limits (Using Antiscalants) †	· Langelier Saturation Index(LSI)	<+1.5
	· Stiff and Davis Saturation Index(SDSI)	<+0.5
	· CaSO ₄	230% saturation
	· SrSO ₄	800% saturation
	· BaSO ₄	6,000% saturation
	· SiO ₂	100% saturation

†The above saturation limits are typically accepted by proprietary antiscalant manufacturers. It is the user's responsibility to ensure proper chemical(s) and concentration are dosed ahead of the membrane system to prevent scale formation anywhere within the membrane system. Membrane elements fouled or damaged due to scale formation are not covered by the limited warranty.

GENERAL HANDLING PROCEDURES

Elements contained in the boxes must be kept dry at room temperature (7–32°C; 40–95°F) and should not be stored in direct sunlight. If the polyethylene bag is damaged, a new preservative solution (sodium bisulfite) must be added and air-tight sealed to prevent drying and biological growth.

Permeate from the first hour of operation should be discarded to flush out the preservative solution.

Elements should be immersed in a preservative solution during storage, shipping and system shutdowns to prevent biological growth and freezing. The standard storage solution contains 1% by weight sodium bisulfite or sodium metabisulfite (food grade). For short term storage (i.e. one week or less) 1% by weight sodium metabisulfite solution is adequate for preventing biological growth.

Keep elements moist at all times after initial wetting.

Avoid excessive pressure and flow spikes.

Only use chemicals compatible with the membrane elements and components. Use of such chemicals may void the element limited warranty.

Permeate pressure must always be equal or less than the feed/concentrate pressure. Damage caused by permeate back pressure voids the element limited warranty.

LENNTECH

info@lennotech.com Tel. +31-152-610-900
www.lennotech.com Fax. +31-152-616-289