

Product Data Sheet



AmberLite[™] FPA900UPS CI Ion Exchange Resin

Food-grade, Uniform Particle Size, High Capacity, Styrenic, Macroporous, Strong Base Anion Exchange Resin for Cane Sugar Decolorization

Description	 AmberLite™ FPA900UPS CI Ion Exchange Resin has been specially designed for the decolorization of liquid sugar syrups. Ion exchange based decolorization technology has been used more effectively and economically than carbon or bone char based technologies. Sugar refiners and soft drink bottlers around the world have installed AmberLite™ FPA900UPS CI to successfully decolorize sucrose solutions. AmberLite™ FPA900UPS CI is a uniform particle size, styrenic, macroporous, high capacity, Type I strong base anion resin. It is an excellent choice for cane sugar decolorization, offering advantages such as: Ready for installation without pre-startup backwashing Less resin lift on backwashing, allowing faster flow for better backwash cleaning; this is well-suited for two-compartment designs with limited backwash allowance Maximum decolorization efficiency due to the macroporous structure Exceptional physical stability, excellent resistance to osmotic shock, and very good organic fouling resistance Uniform particle size distribution, which offers better approximation to plug-flow, facilitating potential OPEX savings from: Enhancement of the regeneration process Reduced rinsing requirements and waste generation Reduced sweetwater and evaporation costs Minimal losses during backwashing due to the absence of small beads
	 Minimal losses during backwashing due to the absence of small beads Styrenic AmberLite[™] FPA900UPS CI can be used as a single component or following
	acrylic AmberLite™ FPA98 CI Ion Exchange Resin for highly-colored feed solutions.
Applications	Cane sugar decolorization

Typical Properties

Physical Properties		
Copolymer	Styrene-divinylbenzene	
Matrix	Macroporous	
Туре	Strong base anion, Type I	
Functional Group	Trimethylammonium	
Physical Form	Off-white to light yellow, opaque, spherical beads	
Chemical Properties		
Ionic Form as Shipped	CI	
Total Exchange Capacity	≥ 1.1 eq/L	
Water Retention Capacity	56-66%	
Particle Size §		
Particle Diameter	$640\pm50\mu m$	
Uniformity Coefficient	≤1.1	
Stability		
Whole Beads	≥95%	
Swelling	$CI^- \rightarrow OH^-$: 15%	
Density		
Particle Density	1.06 g/mL	
Shipping Weight	670 g/L	

[§] For additional particle size information, please refer to the <u>Particle Size Distribution Cross Reference Chart</u> (Form No. 45-D00954-en).

Suggested Operating Conditions

Maximum Operating Temperature (Cl ⁻ form)	80°C (176°F)	
Bed Depth, min.	1000 mm (3.3 ft)	
Flowrates		
Service	2 - 4 BV*/h (or up to 8 BV/h)	
Sweeten-off	Service flowrate for 1.5 – 2 BV	
Backwash	See Figure 1	
Regeneration	2 BV/h	
Slow Rinse	2 BV/h	
Sweeten-on	Service flowrate for 1 BV	
Contact Time		
Regeneration	≥45–60 minutes	
Displacement Rinse	≥ 60 minutes	
Total Rinse Requirement	5 BV	
Regenerant	NaCl+NaOH	
Concentration	10% NaCl 0.2% NaOH	
Level, 100% basis		
Co-current	180 – 200 kg/m ³ (11.3 – 12.5 lb/ft ³)	
Counter-current	150 kg/m ³ (9.4 lb/ft ³)	
Temperature	25–70°C (77–158°F)	


* 1 BV (Bed Volume) = 1 m^3 solution per m^3 resin or 7.5 gal solution per ft^3 resin

Refer to the brochure <u>Ion Exchange Resins for Cane Sugar Decolorization</u> (Form No. 45-D02221-en) for additional information.

Hydraulic Characteristics

Bed expansion of AmberLite[™] FPA9000UPS CI Ion Exchange Resin as a function of backwash flowrate at 25°C (77°F) is shown in Figure 1. The flowrate necessary to achieve a desired bed expansion for other water temperatures can be calculated with the provided equations.

Pressure drop data for AmberLite[™] FPA9000UPS CI as a function of service flowrate and viscosity is shown in Figure 2. These pressure drop expectations are valid at the start of the service run with clean feed.



For other temperatures use:

 $F_T = F_{25^{\circ}C} [1 + 0.008 (1.8T_{\circ C} - 45)]$, where $F \equiv m/h$ $F_T = F_{77^{\circ}F} [1 + 0.008 (T_{\circ F} - 77)]$, where $F \equiv gpm/ft^2$

Product Stewardship

DuPont has a fundamental concern for all who make, distribute, and use its products, and for the environment in which we live. This concern is the basis for our product stewardship philosophy by which we assess the safety, health, and environmental information on our products and then take appropriate steps to protect employee and public health and our environment. The success of our product stewardship program rests with each and every individual involved with DuPont products—from the initial concept and research, to manufacture, use, sale, disposal, and recycle of each product.

Customer Notice DuPont strongly encourages its customers to review both their manufacturing processes and their applications of DuPont products from the standpoint of human health and environmental quality to ensure that DuPont products are not used in ways for which they are not intended or tested. DuPont personnel are available to answer your questions and to provide reasonable technical support. DuPont product literature, including safety data sheets, should be consulted prior to use of DuPont products. Current safety data sheets are available from DuPont.

Please be aware of the following:

• **WARNING:** Oxidizing agents such as nitric acid attack organic ion exchange resins under certain conditions. This could lead to anything from slight resin degradation to a violent exothermic reaction (explosion). Before using strong oxidizing agents, consult sources knowledgeable in handling such materials.



All information set forth herein is for informational purposes only. This information is general information and may differ from that based on actual conditions. Customer is responsible for determining whether products and the information in this document are appropriate for Customer's use and for ensuring that Customer's workplace and disposal practices are in compliance with applicable laws and other government enactments. The product shown in this literature may not be available for sale and/or available in all geographies where DuPont is represented. The claims made may not have been approved for use in all countries. Please note that physical properties may vary depending on certain conditions and while operating conditions stated in this document are intended to lengthen product lifespan and/or improve product performance, it will ultimately depend on actual circumstances and is in no event a guarantee of achieving any specific results. DuPont assumes no obligation or liability for the information in this document. References to "DuPont" or the "Company" mean the DuPont legal entity selling the products to Customer unless otherwise expressly noted. NO WARRANTIES ARE GIVEN; ALL IMPLIED WARRANTIES OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE ARE EXPRESSLY EXCLUDED. No freedom from infringement of any patent or trademark owned by DuPont or others is to be inferred.

DuPont[™], the DuPont Oval Logo, and all trademarks and service marks denoted with [™], sM or [®] are owned by affiliates of DuPont de Nemours Inc. unless otherwise noted. © 2020 DuPont.

