




Membrane Element ESPA2 MAX

Performance	Permeate Flow: Salt Rejection: Boron Rejection (Typical)@ pH = 10:	12,000 gpd (45.4 m ³ /d) 99.6% (99.5% minimum) 93.0 % [†]
Туре	Configuration: Membrane Polymer: Membrane Active Area:	Spiral Wound Composite Polyamide 440 ft ² (40.8m ²)
Application Data*	Maximum Applied Pressure: Maximum Chlorine Concentration: Maximum Operating Temperature: pH Range, Continuous (Cleaning): Maximum Feedwater Turbidity: Maximum Feedwater SDI (15 mins): Maximum Feed Flow: Minimum Ratio of Concentrate to Permeate Flow for any Element: Maximum Pressure Drop for Each Element:	600 psig (4.14 MPa) < 0.1 PPM 113 °F (45 °C) 2-10.6 (1-12)* 1.0 NTU 5.0 75 GPM (17.0 m ³ /h) 5:1 15 psi

* The limitations shown here are for general use. For specific projects, operating at more conservative values may ensure the best performance and longest life of the membrane. See Hydranautics Technical Bulletins for more detail on operation limits, cleaning pH, and cleaning temperatures.

Test Conditions

The stated performance is initial (data taken after 30 minutes of operation), based on the following conditions:



Notice: Permeate flow for individual elements may vary + or - 15 percent. Membrane active area may vary +/-4%. Element weight may vary. All membrane elements are supplied with a brine seal, interconnector, and o-rings. Elements are enclosed in a sealed polyethylene bag containing less than 1.0% sodium meta-bisulfite solution, and then packaged in a cardboard box.

[†]When tested at standard test conditions with 5.0ppm Boron in feed solution.

Hydranautics believes the information and data contained herein to be accurate and useful. The information and data are offered in good faith, but without guarantee, as conditions and methods of use of our products are beyond our control. Hydranautics assumes no liability for results obtained or damages incurred through the application of the presented information and data. It is the user's responsibility to determine the appropriateness of Hydranautics' products for the user's specific end uses. 3/06/15

LENNTECH info@lenntech.com Tel. +31-152-610-900 www.lenntech.com Fax. +31-152-616-289