



LenHFP High Flow Pleated

LenHFP High Flow Polypropylene and Micro-glass Filter Cartridges address your need for absolute rated filter cartridges in high flowrate applications. LenHFP cartridges are designed for use as a direct replacement to the Pall® Ultipleat® High Flow and 3M 740™ series elements. Filtration efficiencies exceed 99%.

Flow Rate vs Pressure Drop



Construction Materials

- Filtration Media**..... Polypropylene or Microglass
- Support Media**..... Polypropylene
- End Caps**..... Polypropylene
- Center Core**..... Polypropylene
- Outer Support Cage**..... Polypropylene
- O-Rings/Gaskets**..... Buna, EPDM, Silicone, Viton®

Operating Conditions

- Change Out ΔP (recommended)**.....35 PSID
- Polypropylene Temperature (max)**__160°F (71°C)
- Microglass Temperature (max)**____200°F (93°C)
- Differential Pressure (max)**.....60 PSID (4.1 bar) at 68°F (20°C)

Food Safety Compliance

Materials of construction comply with FDA regulations for food and beverage contact use as detailed in the US Code of Federal Regulations, 21CFR. Materials used to produce filter media and hardware are deemed safe for use in contact with foodstuffs in accordance with EU Directives 2002/72/EC, 1935/2004, and/or 10/2011.

Dimensions

Length:

HF - 20, 40, 60 inches
HF3 - 39 inches

Outside Diameter:

6.25 inches

Ordering Information

Type	Material	Rating (µ)	A	Length	O-Rings
HFP	PP = Polypropylene	0.45	A= Absolute	20" = HF (50.8 cm)	B = Buna
Retrofits	FG = Microglass	1.0		39" = HF3 (99.1 cm)	E = EPDM
Pall® HF		5.0		40" = HF (101.6 cm)	S = Silicone
HFP		10.0		60" = HF (152.4 cm)	V = Viton®
Retrofits		20.0			
3M™ - 740		50.0			
		100.0			

Pall® is a registered trademark of Pall® Corporation