

Lewatit

PRODUCT INFORMATION LEWATIT[®] MonoPlus S 200 KR

Lewatit[®] **MonoPlus S 200 KR** is a strongly acidic, premium grade, gel-type cation exchange resin with beads of uniform size (monodisperse), in highly regenerated form and purified (extremely low content of desorbable chloride ions) to meet nuclear industry specifications.

Lewatit[®] nuclear resins (Lewatit[®] KR) are noted for their outstanding mechanical and chemical stability and their high osmotic stability.

Because of their excellent hydrodynamic properties, Lewatit[®] KR resins allow particularly high flow rates. The extremely high monodispersity and very low fines content result in particularly low pressure losses compared with standard resins. Used in radioactive water circuits, they provide a number of special tasks and guarantee a water quality that fully complies with the requirement of the nuclear power industry.

Lewatit® MonoPlus S 200 KR is particularly suitable for:

» the removal of cations, including radioactive isotopes, from aqueous solutions (pH control through adsorption of excess ⁷Li)

» the decontamination of circuits in nuclear reactor plants

» the removal of radioactive cations, highly selective for caesium 137

» the treatment of primary coolant e.g. in pressure water reactors

» the purification of steam generator blowdown irrespective of the conditioning with Levoxin (hydrazine), ethanolamine or morpholine

» the removal of activated cleavage or corrosion products, including mechanical filtration of suspended impurities

» the polishing in the primary and secondary sections as a mixed bed component with Lewatit[®] MonoPlus M 800 KR.

Important!

Rinse carefully with demineralized water prior to service or mixing with Lewatit® MonoPlus M 800 KR.

The special properties of this product can only be fully utilized if the technology and process used correspond to the current state-of-the-art. Further advice in this matter can be obtained from Lanxess, Business Unit Liquid Purification Technologies.





Common Description

Delivery form	H⁺
Functional group	Sulfonic acid
Matrix	Styrenic
Structure	Gel
Appearance	Dark brown

Specified Data

Uniformity coefficient		max.	1.1
Mean bead size	d50	mm	0.60 (+-0.05)
Total capacity (delivery		min. eq/L	2.1
form)			



Typical Physical and Chemical Properties

Bulk density for shipment	(+/- 5%)	g/L	790
Density		approx. g/mL	1.23
Water retention (delivery		approx. weight %	45-50
form)			
Volume change (H ⁺ -		max. approx. %	-8
Na⁺)			
Stability pH range			0-14
Storage time (after		max. years	1
delivery)			
Storage temperature		O°	-20 - +40
range			
Friability		average g/bead	600
Friability	>200 g/bead	min. vol %	95
Ionic conversion H ⁺		min. eq. %	99.9

Operation

Operating temperature		max. °C	140
Operating pH range	during exhaustion		2-14
Bed depth for single column		min. mm	800
Bed depth per component in mixed bed		min. mm	500
Back wash bed expansion per m/h (20°C)		%	3.5
Specific pressure loss kPa*h/m² (15°C)		kPa*h/m² (15°C)	1
Max. pressure loss during operation		kPa	250
Specific flow rate		max. BV/h	100





Regeneration

	1		
HCI regeneration	concentration	approx. wt. %	4-6
HCI regeneration	quantity co-current	min. g/L resin	100
HCI regeneration	quantity counter-current	min. g/L resin	55
H ₂ SO ₄ regeneration	concentration	approx. wt. %	1.5-8
H ₂ SO ₄ regeneration	quantity co-current	min. g/L resin	120
H ₂ SO ₄ regeneration	quantity counter-current	min. g/L resin	80
Regeneration contact		min. minutes	20
time			
Slow rinse at		min. BV	2
regeneration flow rate			
Fast rinse at service flow		min. BV	2
rate			

Trace Impurities

Na	max. mg/kg dry resin	50
Fe	max. mg/kg dry resin	30
Cu	max. mg/kg dry resin	5
AI	max. mg/kg dry resin	5
Со	max. mg/kg dry resin	5
Pb	max. mg/kg dry resin	10
Hg	max. mg/kg dry resin	5
SiO ₂	max. mg/kg dry resin	20
Organic Chloride	max. mg/kg dry resin	60





Additional Information & Regulations

Safety precautions

Strong oxidants, e.g. nitric acid, can cause violent reactions if they come into contact with ion exchange resins.

Toxicity

The safety data sheet must be observed. It contains additional data on product description, transport, storage, handling, safety and ecology.

Disposal

In the European Community Ion exchange resins have to be disposed, according to the European waste nomenclature which can be accessed on the internet-site of the European Union.

Storage

It is recommended to store ion exchange resins at temperatures above the freezing point of water under roof in dry conditions without exposure to direct sunlight. If resin should become frozen, it should not be mechanically handled and left to thaw out gradually at ambient temperature. It must be completely thawed before handling or use. No attempt should be made to accelerate the thawing process.

Packaging

The experience has shown that the packaging stability for reliable resin containment is limited to 24 months under the storage conditions described above. It is therefore recommended to use the product within this time frame; otherwise the packaging condition should be checked regularly.



This information and our technical advice – whether verbal, in writing or by way of trials – are given in good faith but without warranty, and this also applies where proprietary rights of third parties are involved. Our advice does not release you from the obligation to check its validity and to test our products as to their suitability for the intended processes and uses. The application, use and processing of our products and the products manufactured by you on the basis of our technical advice are beyond our control and, therefore, entirely your own responsibility. Our products are sold in accordance with the current version of our General Conditions of Sale and Delivery.

