

Lewatit® S 7968 is a Food grade, macroporous adsorber resin without functional groups. It has beads of a uniform size (monodisperse).

It can be used in the extraction / purification of natural or synthetic organic products in the food industry.

In addition, it can be used for the adsorption / removal of:

- anionic, cationic and nonionic surfactants
- chlorinated and nitrated hydrocarbons
- colorants or inert organic materials
- for removing of non-polar organic ingredients of low molecular mass from landfill leachates
- for debittering of fruit juices

Lewatit® S 7968 has the following properties:

- very good mechanical stability and low attrition
- longer resin life time and better regeneration efficiency compared to activated carbon
- high adsorption capacity especially at medium and high feed concentration
- good kinetic performance during adsorption and elution

Prior to industrial application, preliminary tests should be carried out on a laboratory scale, in order to determine the maximum adsorptive capacity and the optimum regenerant. Experience has shown that the maximum capacity of the adsorber resin is reached after the third cycle.

When using **Lewatit® S 7968** to treat potable water and the aqueous solutions listed above, special care should be given to the initial cycles of the new resin. Please refer to the recommended start-up conditions available on request.

The special properties of this product can only be fully utilized if the technology and process used correspond to the current state-of-the-art. Further advice in this matter can be obtained from Lanxess, Business Unit Liquid Purification Technologies.

Common Description

Delivery form	Neutral
Functional group	None
Matrix	Styrenic
Structure	Macroporous
Appearance	White, opaque

Specified Data

Uniformity coefficient		max.	1.1
Mean bead size	d50	mm	0.44-0.54

Typical Physical and Chemical Properties

Bulk density for shipment	(+/- 5%)	g/L	600
Density		approx. g/mL	1.0
Water retention (delivery form)		approx. weight %	54-63
Stability pH range			0-14
Stability temperature range		°C	1-120
Storage time (after delivery)		max. years	2
Storage temperature range		°C	-20 - +40
Surface BET		approx. m ² /g	800
Pore volume		approx. cm ³ /g	1.2
Pore diameter		approx. nm	5-10

Operation

Operating temperature		max. °C	120
Operating pH range	during exhaustion		0-14
Bed depth for single column		min. mm	1000
Back wash bed expansion per m/h (20°C)		%	40 (15°C)
Specific pressure loss kPa*h/m ² (15°C)		kPa*h/m ² (15°C)	1.5
Max. pressure loss during operation		kPa	250
Specific flow rate		max. BV/h	5

This document contains important information and must be read in its entirety.

Regeneration

HCl regeneration	concentration	approx. wt. %	4-6
HCl regeneration	quantity co-current	min. g/L resin	100
HCl regeneration	quantity counter-current	min. g/L resin	55-65
H ₂ SO ₄ regeneration	concentration	approx. wt. %	1.5-3
H ₂ SO ₄ regeneration	quantity co-current	min. g/L resin	150
H ₂ SO ₄ regeneration	quantity counter-current	min. g/L resin	80
NaOH regeneration	concentration	approx. wt. %	2-6
NaOH regeneration	quantity co-current	min. g/L resin	100
NaOH regeneration	quantity counter-current	min. g/L resin	60
Regeneration contact time		min. minutes	30
Slow rinse at regeneration flow rate		min. BV	2
Fast rinse at service flow rate		min. BV	4

This document contains important information and must be read in its entirety.

Additional Information & Regulations

Safety precautions

Strong oxidants, e.g. nitric acid, can cause violent reactions if they come into contact with ion exchange resins.

Toxicity

The safety data sheet must be observed. It contains additional data on product description, transport, storage, handling, safety and ecology.

Disposal

In the European Community ion exchange resins have to be disposed, according to the European waste nomenclature which can be accessed on the internet-site of the European Union.

Storage

It is recommended to store ion exchange resins at temperatures above the freezing point of water under roof in dry conditions without exposure to direct sunlight. If resin should become frozen, it should not be mechanically handled and left to thaw out gradually at ambient temperature. It must be completely thawed before handling or use. No attempt should be made to accelerate the thawing process.

Packaging

The experience has shown that the packaging stability for reliable resin containment is limited to 24 months under the storage conditions described above. It is therefore recommended to use the product within this time frame; otherwise the packaging condition should be checked regularly.

LENNTECH
WATER TREATMENT SOLUTIONS
info@lennotech.com Tel. +31-152-610-900
www.lennotech.com Fax. +31-152-616-289

This information and our technical advice – whether verbal, in writing or by way of trials – are given in good faith but without warranty, and this also applies where proprietary rights of third parties are involved. Our advice does not release you from the obligation to check its validity and to test our products as to their suitability for the intended processes and uses. The application, use and processing of our products and the products manufactured by you on the basis of our technical advice are beyond our control and, therefore, entirely your own responsibility. Our products are sold in accordance with the current version of our General Conditions of Sale and Delivery.

This document contains important information
and must be read in its entirety.